





No	WLCP Part No.	Description	Part No	Cold Only	Hot & Cold	Stocked?	
Consumables							
1	10-2350	8W UV Lamp Assembly with Glow starter	CT-2001-100-00	X	X	Yes	
2	10-4029	Hot Tank Stainless Steel 1.5 Liter (87°C - 189°F)	HT-3024		X	Yes	
Option	FT-0035	GAC Filter - 10" Carbon Activated Inline Filter - Optional <i>Filter Element PN FT-0038-WLT</i>	FT-0035-IL-WLT	X	X	Yes	
Option	FT-0063	Carbon Block - 10" CBC 1-Micron Lead and Cyst Reduction Inline Filter Optional <i>Filter Element PN FT-0064-WLT</i>	FT-0063-IL-WLT	X	X	Yes	
Option	FT-0053	Sediment Filter - 10" Sediment 20 Micron Inline Filter Optional <i>Filter Element PN FT-0055-WLT</i>	FT-0053-IL-WLT	X	X	Yes	
Recommended Spare Parts							
2.1	12-1360	Overload with Manual Reset - 105°C (221°F) <i>Recommend stocking 2 each per every 10 units purchased</i>	HT-3012		X	Yes	
2.2	12-6900	Hot Tank Supplemental Steel Enclosure <i>Recommend stocking 2 each per every 10 units ordered</i>	ST-8290		X	Yes	
3		MS DC Solenoid Valve SWV24-01	PU-0017-L00-00	X	X	Yes	
4	CU-0001	Solenoid Cushion <i>Recommend stocking 2 each per every 10 units purchased</i>	CU-0001	X	X	Yes	

5	10-2500	Black O-Ring for Quartz Sleeve <i>Recommend stocking 1 each per every 10 units ordered</i>	CT-2006	X	X	Yes	
6	10-1400	Quartz Sleeve for 8W Lamp <i>Recommend stocking 1 each per every 10 units ordered</i>	CT-2002	X	X	Yes	
7	10-3010	UV Lamp Ballast 120V 60Hz 8W	EL-5006-A CN	X	X	Yes	
8	PL-1013	Blue Faucet Nipple	PL-1013	X	X	Yes	
8.1	10-2600	White Silicon Faucet O-Ring <i>Recommend stocking 2 each per every 10 units ordered</i>	CT-2007	X	X	Yes	
9	12-5220	Silicone Button Key Mat AFL HCA	PL-1206-A		X	Yes	
10	PL-1013-G	Stainless Steel Gauze for Faucet	PL-1013-G	X	X	Yes	
11	12-5230	WL2200 Silver Drip Tray Grill	PL-1152-A	X	X	Yes	
12		Canteen wl2200 Drip Tray Body – WL & Bio logo	PL-0269-L00-00	X	X	Yes	
Not Shown	01-2076	ScaleKleen <i>Recommend stocking 5 each per every 10 units ordered</i>	NA	X	X	Yes	
Remaining Parts							
13	PL-1212-CN	Faucet HCA Assembly	PL-1212-CN		X	Yes	


14	12-8050	Front Panel for Drip Tray Insert <i>when purchasing, also request Hot Water Caution Label LP-7169 / 12-0001 to adhere to front of this panel.</i>	PL-1146	X	X	Yes	
14.1	12-0001	Hot Water Caution Label Adhere to Front Panel for Drip Tray Insert	LP-7169		X	Yes	
15	12-5285	AFL PCB Cover	PL-1303	X	X	Yes	
16		Canteen WL2200 Display PCB	EN-0109-L00-00	X	X	Yes	
17		Canteen WL2200 HCA Front Hatch Panel	PL-0270-L00-00	X	X	Yes	
18	10-2701	Stainless Steel Insert for Faucet	PL-1088	X	X	Yes	
19	12-8058	Side Panel Plastic Handle	PL-1123	X	X	Yes	
20	12-8052	Front Lower Panel	PL-1148	X	X	Yes	
21		Front Lower Insert Panel	PL-1188-A	X	X	Yes	
22	Purchase from John Guest	JG Equal Elbow Connector 1/4" (PI0308S)	PU-4008	X	X	No	
23	Purchase from John Guest	JG Reducing Elbow Connector 5/16" * 1/4" (PI211008S)	PU-4007	X	X	No	

24	Purchase from John Guest	JG Equal Tee Connector 1/4" (P10208S)	PU-4011	X	X	No	
25	12-8006	Filter Bracket	ST-8138	X	X	Yes	
26	10-3099	3" Filter Clip	PU-4024	X	X	Yes	
27	10-3098	2" Filter Clip for In-Line Filter	PU-4025	X	X	Yes	
28	11-2065	Unit Control Rubber Feet	ST-8167CN	X	X	Yes	
29	12-8004	WL2000 Down Base	ST-8137	X	X	Yes	
30.1		LG Compressor 120V R134A CSB035LJCM	CO-0020-L00-00	X	X	Yes	
30.2		Compressor Capacitor	CO-0019-L00-00	X	X	Yes	
30.3		Capacitor Bracket	ST-0216-L00-00	X	X	Yes	
30.4		PTC Relay	CO-0017-L00-00	X	X	Yes	
30.5		Overload Protector	CO-0018-L00-00	X	X	Yes	
30.6	12-1001	Filter Dryer	CO-9008	X	X	Yes	

31	10-3067	Bulkhead Union ¼" x ¼" John Guest P/N PI1208S	PU-4028	X	X	Yes	
32	12-8102	Wire Condenser	CO-9027	X	X	Special Order	
33	12-8002	Back Panel Silver	ST-8135	X	X	No	
34	12-1101	Cold Tank Thermostat	CT-2016	X	X	Yes	
34.1	LP-0326	Cold Thermostat Cover Label	PL-0326-L00-00	X	X	Yes	
35		Power Line Noise Filter, ElectroMagnetic Interference filter (EMI)	EL-0061-L00-00	X	X	Yes	
36	10-3014	Fuse Holder and Fuse 120V / 15A with One Wire	EL-5053	X	X	Yes	
36.1	10-3013	Fuse 120V / 15A	EL-5010	X	X	Yes	
37	12-5600	Red Compressor and Heater Switch	EL-5019-A	X	X	Yes	
38	12-8003	Upper Shelf	ST-8136-R2	X	X	Yes	
39	12-3117	Power Transformer 120V	EL-5003-A	X	X	Yes	
Not Shown		4W UV Fixing Rubber <i>Included in UV Lamp Assembly</i>	PL-0235-L00-00	X	X	Yes	
41	12-1210	UV Lamp Retaining Threaded Nut	PL-1128	X	X	Yes	

42	12-5245	Main PCB Bracket	ST-8165-CN	X	X	Yes	
Not Shown	10-3017	PCB Stand-off Pin	EN-6059	X	X	Yes	
44	NA	Cold Tank 4 Liter Assembly with UV Holder	CT-2050	X	X	No	
45	12-5260	WL2200 Top Cover Silver	PL-1199-C	X	X	Yes	
46	10-3062	JG LLDPE Tube - Blue 8mm John Guest P/N PE-0806-100M-B	PU-4014	X	X	Yes	
47	19-1054	JG LLD PE Tube - Blue O.D.1/4"John Guest P/N PE-08-BI-1000F-B	PU-4031	X	X	Purchase from John Guest	
48	10-7040	Silicon Tube 5/16" for Hot Water	PU-4064		X	Yes	
Not Shown	10-3007	Power Cord 120V – 1840 mm	EL-5001-B	X	X	Yes	
49	12-3155	Leak Tray	PL-1294-A	X	X	Yes	
49.1	12-3180	Leak Containment Tray Clip (sensor 0.5mm)	ST-8207-CN	X	X	Yes	
49.2	NA	Leak Sensor Wire	EL-5074-A	X	X	Yes	
50	12-5315	WL2200 Main PCB HCA & CA -w/ leak detection	EN-6102-A	X	X	Yes	
51	12-5200	WL2000 FS Side Panel L/R Silver Handle Hole	ST-8249	X	X	Yes	

ECOSTREAM PLUS COUNTER TOP WATER FLOW DIAGRAM



ECOSTREAM PLUS TOWER WATER FLOW DIAGRAM

